


D-SUB FEMALE CONNECTOR		
PIN No.	WIRE COLOUR	ASSIGNMENT
1		NC
2	PK	CAN-
3		NC
4		NC
5		NC
6	BU	GND
7	GY	CAN+
8		NC
9		NC
HOUSING	SCHIELDING	

120Ω im Sub-D Stecker



Connector: JST-PHDR-8VS

JST PHDR-8VS		
PIN NO.	WIRE COLOUR	ASSIGNMENT
1	BU	GND+SCHELDING
2		NC
3		NC
4		NC
5	PK	CAN-
6	GY	CAN+
7	BN	GND
8	WH	+UB extern

twisted
twisted

AMP Mini Mate-N-Lok
4 pole
Art.-No: 0-0172167-1

CAN+
CAN-
GND

Position	Application 1	Application 2	Lot
10	Heat shrink tube	Length: 15/50mm	2/1
20	JST PHDR-8VS	8 pole	1
30	D-Sub 9 pole Female Connector	9 pole	1
40	Shielding	150mm	1
50	AMP Connector Mini Mat-N-Lok	4 pole	1

AMP CONNECTOR	
PIN NO.	ASSIGNMENT
1	CAN +
2	CAN -
3	GND
4	NC

twisted

				 Nanotec [®] PLUG & DRIVE	SCALE FREE	APVD	G.S.	19.08.10	CABLE SET SMCI12
					X ±0.5	CHKD			
					1PL ±0.2	DRN	J.W.	19.08.10	ZK-SMCI12-3
REV	DESCRIPTION	DATE	APVD		2PL ±0.1	SIGNATURE	DATE		
					ANGLE ±30'				