



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Length „A“ mm	Weight kg
DB22M01	4	0.8	0.265	0.795	24	4800	3.02	0.66	45	0.07
DB22L01	7.7	2.2	0.62	1.6	24	3500	3.55	1.32	68	0.13

DIMENSIONS (IN MM)

