



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Length „A“ mm	Weight kg
DB28S01	4.2	0.5	0.45	1.3	15	8000	1.43	2.35	28	0.06
DB28M01	14.6	1.4	0.95	2.7	24	10000	1.69	3.69	38	0.082
DB28L01	20.9	5	1.45	4.5	24	4000	3.56	10.98	77	0.195

DIMENSIONS (IN MM)

