



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Length „A“ mm	Weight kg
DB41S024030-A	22	7	1.3	4.4	24	3000	5.42	48	40.3	0.3
DB41M024030-A	50	16	3	9.2	24	3000	5.41	101	60.3	0.45
DB41L024030-A	82	26	4.8	14.8	24	3000	5.4	154	80.3	0.65
DB41C024030-A	113	36	6.7	22.2	24	3000	5.4	207	100.3	0.8

ACCESSORIES



- ZD-D28** Damper
- ZD-D40** Damper
- ZD-DF40** Damper

DIMENSIONS (IN MM)

