



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Length „A“ mm	Weight kg
DB56L036030-A	94	30	4	12	36	3000	7.3	260	76	1
DB56C036030-A	141	45	5.4	16.2	36	3000	8	360	96	1.1
DB56D036030-A	188	60	7.5	22.5	36	3000	8	460	116	1.2

DIMENSIONS (IN MM)

