

DB87

Brushless DC Motor



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Length „A“ mm	Weight kg
DB87S01-S	220	70	6.25	19	48	3000	11.2	800	86	1.85
DB87M01-S	440	140	10.77	32.31	48	3000	13	1600	113	2.6
DB87L01-S	660	210	17.95	53.85	48	3000	11.7	2400	140	4

ACCESSORIES



ZD-D56 Damper

DIMENSIONS (IN MM)

DB87

