



### OPTIONS



### VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm <sup>2</sup>	Length „A“ mm	Weight kg
DBL36S024048-A	7.5	1.5	0.5	1.5	24	4800	3	6	30	0.12
DBL36M024048-A	18	3.5	1	3	24	4800	3.5	12	40	0.16
DBL36L024045-A	33	7	1.9	5.7	24	4500	3.7	27	57	0.25

### DIMENSIONS (IN MM)

