



### OPTIONS



### VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm <sup>2</sup>	Length „A“ mm	Weight kg
DS16S012220-A	3.7	0.16	0.4	1.18	12	22000	0.406	4	28	0.03
DS16M024250-A	10	0.4	0.5	1.6	24	25000	0.75	6.6	40	0.04
DS16L024240-A	25	1	1.33	4	24	24000	0.748	10.2	56	0.065

### DIMENSIONS (IN MM)

