



### CAUTION



Please note that the GPLL gearboxes are only available together with a motor.

### TECHNICAL DATA

<b>Service Life*</b>	1000
<b>For Motor Size</b>	NEMA 8, NEMA 11
<b>Operating Temperature</b>	-10 to +80 °C
<b>Admissible Axial Shaft Load</b>	7 N
<b>Admissible Radial Shaft Load</b>	10 N
<b>Max. Input Speed</b>	9000 rpm

\*The estimated service life is an approximate value based on the listed nominal torques and an ambient temperature of 30 °C. There are no data available for differing conditions as the environmental factors and operating conditions may vary greatly.

### VERSIONS

Type	Reduction Ratio	Rated Output Torque Nm	Max. Output Torque Nm	Efficiency %	Max. Backlash (arc minutes)	Length „L“ mm	Flange Length L1 mm	Weight kg
GPLL22-5	4.66	0.2	0.6	80	150	21.8	5	0.046
GPLL22-25	25.2	0.3	0.9	70	150	28	5	0.051
GPLL22-90	89.72	0.4	1.2	60	150	34.2	5	0.058

### DIMENSIONS (IN MM)

