



SOFTWARE



MOTOR-CONTROLLERS

TECHNICAL DATA

Temperature Range	-10 °C - 40 °C
Number of Digital Inputs	6
Type of Digital Inputs	24 V, 5/24 V switchable
Digital Outputs	2
Type of Digital Output	open-drain (max. 24 V/100 mA)
Number of Analog Inputs	1
Type of Analog Input	0-20 mA/0-10 V switchable

VERSIONS

Type	Interface	Rated Current (RMS) A	Peak Current (RMS) A	Operating Voltage VDC	Encoder Input	Brake Output	Corresponding Motors	Weight kg
C5-01	USB, IO (clock direction; analog)	6	6	12 - 48	-	-	Stepper Motors	0.13

ACCESSORIES



ZK-MICROUSB
Micro USB Cable 1.5 m

CAUTION



We recommend using a charging capacitor of sufficient size to stabilize the operating voltage.

Open-Loop Stepper Motor Controller/Drive

DIMENSIONS (IN MM)

C5-01

