



OPTIONS



SOFTWARE



TECHNICAL DATA

Operating Voltage	12 VDC - 48 VDC
Number of Digital Inputs	4 - 6
Type of Digital Inputs	24 V, 5/24 V switchable
Number of Analog Inputs	1
Type of Analog Input	0-20 mA/0-10 V switchable
Digital Outputs	2 - 3
Type of Digital Output	open-drain (max. 24 V/100 mA)
Encoder	✓
Encoder Type	single-turn absolute
Encoder Resolution	1024 CPR

VERSIONS

Type	Holding Torque Ncm	Rated Current (RMS) A	Peak Current (RMS) A	Interface	Length mm	Weight kg
PD2-C4118L1804	50	1.8	3	USB, IO (clock direction; analog), CANopen	74	0.5

ORDER IDENTIFIER

PD2-C4118L1804-E-
 01 = USB,IO (clock direction; analog)
 08 = CANopen



ACCESSORIES



ZK-MICROUSB
 Micro USB Cable 1.5 m
ZK-PD4-C-CAN-4-500-S
 CAN in/out Cable 0.5m
Z-K4700/50 Charging Capacitor



CAUTION

We recommend using a charging capacitor of sufficient size to stabilize the operating voltage.

DIMENSIONS (IN MM)



TORQUE CURVES

