



OPTIONS



VERSIONS

Type	Current per Winding A	Holding Torque Ncm	Resistance per Winding Ohm	Inductance per Winding mH	Rotor Inertia gcm ²	Weight kg	Length „A“ mm
SC3518S1204	1.2	10	1.7	1.5	11	0.15	30
SC3518M1204	1.2	18	2.5	2.9	20	0.18	39.5
SC3518L1204	1.2	32	3.8	5.2	43	0.3	56.5


ORDER IDENTIFIER

SC3518S1204-
A = single shaft end
B = double shaft end

ACCESSORIES

ZK-JST-EHR-6-0.5M-S Motor Cable 0.5 m
ZD-D28 Damper
ZD-D40 Damper

DIMENSIONS (IN MM)



TORQUE CURVES

