



## VERSIONS

Type	Number of Poles	Cable Length m	Connector Type	Shielding	Suitable for
ZK-M12-5-2M-1-AFF	5	2	Straight	✓	AS28, AS41, AS59, PD4-E, PD4-EB
ZK-M12-5-2M-2-AFF	5	2	Angled	✓	AS28, AS41, AS59, PD2-N-IP, PD4-N-IP
ZK-M12-5-5M-1-AFF	5	5	Straight	✓	AS28, AS41, AS59
ZK-M12-5-5M-2-AFF	5	5	Angled	✓	AS28, AS41, AS59, PD2-N-IP, PD4-N-IP
ZK-M12-8-2M-1-AFF	8	2	Straight	✓	AS41, AS59
ZK-M12-8-2M-2-AFF	8	2	Angled	✓	AS41, AS59
ZK-M12-8-5M-1-AFF	8	5	Straight	✓	AS41, AS59
ZK-M12-8-5M-2-AFF	8	5	Angled	✓	AS41, AS59
ZK-M12-12-2M-1-AFF	12	2	Straight	✓	AS89, ASB42, ASB87, PD4-E, PD4-EB
ZK-M12-5-2M-1-B-S	5	2	Straight	✓	PD4-E, PD4-EB
ZK-M12-5-2M-1-A-S-M	5	2	Straight	✓	PD4-E, PD4-EB
ZK-M12-4-2M-1-D-RJ45	4	2	Straight	✓	PD4-E, PD4-EB
ZK-M12-8-2M-2-PADP	8	2	Angled	✓	AS41, AS59
ZK-M12-12-2M-2-PADP	12	2	Angled	✓	ASB42, ASB87
ZK-M12M-M8F-5-200-S	5	0,2	Straight	✓	PD2-C-IP, PD2-CB-IP, PD4-E, PD4-EB
ZK-M12M-M12F-5-500-S	5	5	Straight	✓	PD4-E, PD4-EB
ZK-M12-17-1M-2-S-FIN	17	1,5	Angled	✓	PD2-N-IP, PD4-N-IP