



| | | | |
|----------------|------|------|---------|
| Major diameter | [mm] | 10.0 | 0/-0.18 |
| Minor diameter | [mm] | 7.5 | 0/-0.31 |



| | | | | | | | | | | | |
|----------|-----------------------|----------|------------|------------------|------------|-----------------|--|------------------|---|--------------|--|
| ISO 8015 | | ISO 1302 | | ISO 2768 mK | | ISO 13715 | | Material: 1.4021 | | Weight: - kg | |
| | | | | Drawn | 25.04.2018 | Name | | ZST10-2-300-1 | | | |
| | | | | Checked | 11.12.2018 | Rehse_P | | | | | |
| | | | | Approved | 11.12.2018 | Rehse_P | | | | | |
| 04 | change tol. maj. dia. | Rehse_P | 12.12.2018 | PLUG & DRIVE | | 06200056 | | | - | | |
| REV | Rev. Text | Name | Rel. Date | | | State: Released | | Rev: 04 | | P | |