





GPLK42-4.3 for DF45

GPLK42-4.3 for NEMA 17



use EJOT Delta PT screw
WN5452 40x...
Tmax. = 1.6 +0.2 Nm



GEARBOX SPECIFICATION	
Reduction Ratio	4.25
No. of Stages	1
Rated Output Torque	Nm 4.0
Max. Output Torque	Nm 8.0
Max. Input Speed	rpm 5000
Backlash	° 1.5
Efficiency	% 75
Lifetime	h 5000
Max. Axial Force	N 40
Max. Radial Force (shaft middle)	N 40
Ambient Temperature	°C -15 ... 40

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 0.145 kg	
		Date	Name	GPLK42-4.3	
		Drawn	05.07.2018		Schneid_A
		Checked	23.10.2018		Naubert_A
		Approved	23.10.2018	Naubert_A	
		Nanotec PLUG & DRIVE		12200031	
REV	Rev. Text	Name	Rel. Date	State: Released	
				Scale: 1 : 1 A4	
				Rev: - P	