



A B C D E F

DIMENSION (UNIT : mm)

1
2
3
4
5



6	DIN 2768-m		Oberfläche:		NANOTEC	SCALE FREE	APVD	M 8:1	<i>Toleranz Hülsen</i>
	Material: 1.4305					X ±0.5	CHKD		
					MK-DH-6.35-8	1PL ±0.2	DRN	20.10.2006	DWG.NO
REV	DESCRIPTION	DATE	APVD			2PL ±0.1	SIGNATURE	DATE	MK-DH-6.35-8
						ANGLE ±30'			

A B C D E F