


DIMENSION (UNIT: mm)



X1	
PIN ASSIGNMENT: Phoenix MC 0.5/5-G-2.5	
Pin No.	Function
1	GND
2	CAN_L
3	CAN_SHLD
4	CAN_H
5	CAN_V+

X2	
PIN ASSIGNMENT: D-Sub, 9Pins, Plug	
Pin No.	Function
1	N.C.
2	CAN_L
3	GND
4	N.C.
5	CAN_SHLD
6	GND
7	CAN_H
8	N.C.
9	CAN_V+

X3	
PIN ASSIGNMENT: D-Sub, 9Pins, Socket	
Pin No.	Function
1	N.C.
2	CAN_L
3	GND
4	N.C.
5	CAN_SHLD
6	GND
7	CAN_H
8	N.C.
9	CAN_V+

X4 / X5	
PIN ASSIGNMENT: JST, BM04B-GHS-TBT	
Pin No.	Function
1	CAN_V+
2	CAN_H
3	CAN_L
4	GND

X10	
PIN ASSIGNMENT: RJ45, 8Pins, Dual Port, Socket	
Pin No.	Function
1	CAN_H
2	CAN_L
3	GND
4	N.C.
5	N.C.
6	CAN_SHLD
7	GND
8	CAN_V+

SW1:
120 Ohm Termination Resistor



APVD G.M. 01.02.17
CHKD

REV	DESCRIPTION	DATE	DRN

Surface specification DIN ISO 1302
General tolerances DIN ISO 2768- cH
Work piece edge DIN ISO 13715

DRN A.S. 01.02.17
SIGNATURE DATE

DWG.NO
EB-CAN-Adapter