



Thread code:UGFC	
Thread type	ACME
Major diameter [mm]	4.636...4.763
Minor diameter [mm]	2.868...3.239
Lead	5.08
Pitch	1.27
Starts	4
Thread per inch	20

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: 1.4305	
				Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE
A	-	09.12.2020	X T				DRN	X T	
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	13.03.2018