



Thread code UKBN	
Thread type	ACME
Major diameter [mm]	6.223...6.350
Minor diameter [mm]	4.107...4.509
Lead	1.5875
Pitch	1.5875
Starts	1
Thread per inch	16

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu (±1.4570)	
				 Nanotec [®] PLUG & DRIVE			Name	Date	THREADED SPINDLE
B	-	25.07.22	X T				DRN	L W	
A	-	09.12.20	X T				CHKD	GYQ	12.04.2018
REV	DESCRIPTION	DATE	DRN	APVD	P.R.	12.04.2018			