



| Thread code UKGI | |
|---------------------|---------------|
| Thread type | ACME |
| Major diameter [mm] | 6.223...6.350 |
| Minor diameter [mm] | 4.107...4.509 |
| Lead | 6.350 |
| Pitch | 1.5875 |
| Starts | 4 |
| Thread per inch | 16 |

| | | | | | | | | | |
|-----|-------------|----------|-----|---|---------------------------------------|--|----------------------------------|---|------------------|
| | | | |  | Surface specification DIN ISO 1302 | General tolerances DIN ISO 2768- mK | Work piece edge DIN ISO 13715 | Scale: Material: SUS303Cu (± 1.4570) | |
| | | | |  Nanotec [®] PLUG & DRIVE | | | Name | Date | THREADED SPINDLE |
| B | - | 25.07.22 | X T | | | | DRN | L W | |
| A | - | 09.12.20 | X T | | | | CHKD | GYQ | 29.09.2017 |
| REV | DESCRIPTION | DATE | DRN | | | | APVD | A.N. | 29.09.2017 |