



Thread code TSCA	
Thread type	Trapezoid
Major diameter [mm]	9.820...10.000
Minor diameter [mm]	7.191...7.500
Lead	2
Pitch	2
Starts	1
Thread per inch	12.7

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: 1.4305	
							Name	Date	
					DRN	X T	29.04.2020	THREADED SPINDLE SCREW-ABA-TSCA-200	
					CHKD	GYQ	29.04.2020		
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	29.04.2020