



WHEEL DRIVE SPECIFICATION

	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx	11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
No. of Stages	2			
Rated Output Torque	Nm 19.2	24.6	28.6	29.1
Max. Output Torque	Nm 32.9	39.4	39.4	39.4
Rated Input Speed	rpm 3500	3500	3500	3500
Max. Input Speed	rpm 4685	5968	8304	8988
Backlash	° <30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	% 94	94	94	94
Inertia	10 ⁻⁶ kg m ² 58	31	19	12
Load Capacity	kg 400			
Wheel Material	Vulkollan			
Ambient Temperature	°C -15...+90			
Protection Class	IP54			

03

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 4.6kg	
			Date	Name	
			Drawn	06.09.2019	Rehse_P
03	Load capacity updated	Micheli_M	30.06.2020	Reviewed	13.09.2019
02	specifications updated	Micheli_M	31.03.2020	Released	13.09.2019
01	First Released				Naubert_A
REV	Rev. Text	Name	Date		
				06200347	
				Scale: 1 : 2	
				A3 Page 1	
				State: Released	
				Rev: 03	
				CONFIDENTIAL	

WD14050-56xx-60C