



WHEEL DRIVE SPECIFICATION

		11 (10.84)	16 (15.51)	20 (20.03)	26 (25.71)
Reduction Ratio xx					
No. of Stages		2			
Rated Output Torque	Nm	19.2	24.6	28.6	29.1
Max. Output Torque	Nm	32.9	39.4	39.4	39.4
Rated Input Speed	rpm	3500	3500	3500	3500
Max. Input Speed	rpm	4685	5968	8304	8988
Backlash	°	<30 arcmin	<30 arcmin	<30 arcmin	<30 arcmin
Efficiency	%	94	94	94	94
Inertia	10 ⁻⁶ kg m ²	106	56	33	21
Load Capacity	kg	400			
Wheel Material		Vulkollan			
Ambient Temperature	°C	-15...+90			
Protection Class		IP54			



		ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: 4.5kg	
		Date	Name				
04	Load capacity updated	30.06.2020	Micheli_M	Drawn	11.09.2019	WD20050-56xx-80X	
03	specifications updated	31.03.2020	Micheli_M	Reviewed	16.09.2019	Scale: 1 : 2	
02	-	11.11.2019		Released	16.09.2019	A3 Page 1	
01	First Released	11.11.2019				06200363	
REV	Rev. Text	Name	Date			State: Released	Rev: 04

