




Front view and mounting



Side view




Rear view



SPECIFICATION	CONNECTION		BIPOLAR	
	UNIPOLAR OR BIPOLAR-1 WINDING		SERIAL	PARALLEL
VOLTAGE (VDC)	3.38			
AMPS/PHASE	2.6		1.84	3.68
RESISTANCE/PHASE (Ohms)@25°C	1.3±15%		2.6±15%	0.65±15%
INDUCTANCE/PHASE (mH) @1KHz	1.8±20%		7.2±20%	1.8±20%
HOLDING TORQUE (Nm) [lb-in]	0.75 [6.637]		1.06 [9.381]	1.06 [9.381]
DETENT TORQUE (Nm) [lb-in]	0.0225 [0.199]			
STEP ANGLE (°)	0.9			
STEP ACCURACY (NON-ACCUM)	±5%			
ROTOR INERTIA (Kg-m ²) [lb-in ²]	2.75x10 ⁻⁵ [0.094]			
WEIGHT (Kg) [lb]	0.65 [1.433]			

PERMISSIBLE RADIAL+AXIAL FORCE




	AXIAL-FORCE Fa (N)	
	Fa=10	
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]	DISTANCE a (mm)	5 10 15 20
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)	RADIAL-FORCE Fr (N)	130 90 70 52
INSULATION CLASS B 130° [266°F]		AXIAL RADIAL
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)	SHAFT PLAY (mm)	0.075 0.025
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)	AT LOAD MAX: (N)	10 5.0

UNIPOLAR	TYPE OF CONNECTION (EXTERN)			MOTOR	
	1WINDING	BIPOLAR SERIAL	BIPOLAR PARALLEL	LEADS	WINDING
A	A	A	A	RED	A
COM				RED/WHT	
A\		A\	A\	BLK/WHT	A\
B	B	B	B	BLK	B
COM				GRN	
B\		B\	B\	GRN/WHT	B\
				YEL/WHT	
				YEL	

FULL STEP 2 PHASE-Ex., WHEN FACING MOUNTING END (X)

STEP	A	B	A\	B\	CCW	CW
1	+	+	-	-		
2	-	+	+	-		
3	-	-	+	+		
4	+	-	-	+		

WIRING DIAGRAM



REV	DESCRIPTION	DATE	APVD	NANOTEC:
				ST5709S2608

SCALE	APVD	DATE
FREE	S.H.a.	15.01.07
X ±0.5	CHKD	
1PL ±0.2	DRN	J.W. 05.07.06
2PL ±0.1	SIGNATURE	DATE
ANGLE ±30'		

STEPPING MOTOR	
DWG.NO	ST5709S2608