



Major diameter	[mm]	5.0	0/-0.15
Minor diameter	[mm]	3.7	0/-0.462



Surface specification  
DIN ISO 1302

General tolerances  
DIN ISO 2768- mK

Work piece edge  
DIN ISO 13715

Scale: 2:1  
Material: 1.4404

REV	DESCRIPTION	DATE	DRN
2	revise chart	21.06.17	A.S.
1	revise drawing	08.06.17	A.S.



	Name	Date
DRN	A.S.	02.04.2013
CHKD	G.S.	02.04.2013

THREADED SPINDLE

ZST5-2-300-1