



SPECIFICATION		CONNECTION	DELTA	INPUT CONNECTION		PERMISSIBLE RADIAL+AXIAL FORCE ROTOR SPRING-MOUNTED IN AXIAL DIRECTION	X1																																			
NO. OF POL./PHASE	8/3							<table border="1"> <thead> <tr> <th>Pin No.</th> <th>Function</th> </tr> </thead> <tbody> <tr><td>a1</td><td>GND</td></tr> <tr><td>a2</td><td>+UB (12-48V)</td></tr> <tr><td>a3</td><td>INPUT 1 (24V)</td></tr> <tr><td>a4</td><td>INPUT 2 (24V)</td></tr> <tr><td>a5</td><td>INPUT 3 (24V)</td></tr> <tr><td>a6</td><td>ANALOG INPUT (0-10V/0-20mA)</td></tr> <tr><td>a7</td><td>OUTPUT 1 (open drain)</td></tr> <tr><td>a8</td><td>OUTPUT 2 (open drain)</td></tr> <tr><td>b1</td><td>GND</td></tr> <tr><td>b2</td><td>+10V VOLTAGE SUPPLY</td></tr> <tr><td>b3</td><td>-INPUT 4/-ENABLE (5V/24V)</td></tr> <tr><td>b4</td><td>INPUT 4/ENABLE (5V/24V)</td></tr> <tr><td>b5</td><td>-INPUT 5/-DIRECTION (5V/24V)</td></tr> <tr><td>b6</td><td>INPUT 5/DIRECTION (5V/24V)</td></tr> <tr><td>b7</td><td>-INPUT 6/-CLOCK (5V/24V)</td></tr> <tr><td>b8</td><td>INPUT 6/CLOCK (5V/24V)</td></tr> </tbody> </table>		Pin No.	Function	a1	GND	a2	+UB (12-48V)	a3	INPUT 1 (24V)	a4	INPUT 2 (24V)	a5	INPUT 3 (24V)	a6	ANALOG INPUT (0-10V/0-20mA)	a7	OUTPUT 1 (open drain)	a8	OUTPUT 2 (open drain)	b1	GND	b2	+10V VOLTAGE SUPPLY	b3	-INPUT 4/-ENABLE (5V/24V)	b4	INPUT 4/ENABLE (5V/24V)	b5	-INPUT 5/-DIRECTION (5V/24V)	b6	INPUT 5/DIRECTION (5V/24V)	b7	-INPUT 6/-CLOCK (5V/24V)	b8
Pin No.	Function																																									
a1	GND																																									
a2	+UB (12-48V)																																									
a3	INPUT 1 (24V)																																									
a4	INPUT 2 (24V)																																									
a5	INPUT 3 (24V)																																									
a6	ANALOG INPUT (0-10V/0-20mA)																																									
a7	OUTPUT 1 (open drain)																																									
a8	OUTPUT 2 (open drain)																																									
b1	GND																																									
b2	+10V VOLTAGE SUPPLY																																									
b3	-INPUT 4/-ENABLE (5V/24V)																																									
b4	INPUT 4/ENABLE (5V/24V)																																									
b5	-INPUT 5/-DIRECTION (5V/24V)																																									
b6	INPUT 5/DIRECTION (5V/24V)																																									
b7	-INPUT 6/-CLOCK (5V/24V)																																									
b8	INPUT 6/CLOCK (5V/24V)																																									
VOLTAGE RATED (VDC)	48					AXIAL-FORCE $F_a$ (N)	$F_a=10$																																			
CURRENT RATED/PEAK (AMP)	3.3/10					DISTANCE $a$ (mm)	20																																			
TORQUE RATED/PEAK (Nm)	0.25/0.75					RADIAL-FORCE $F_r$ (N)	28																																			
POWER RATED (W)	105					SHAFT PLAY (mm)	AXIAL	0.1																																		
SPEED RATED/NO LOAD (RPM)	4000/6500						RADIAL	0.02																																		
ROTOR INERTIA (Kg-m <sup>2</sup> )	$9.6 \times 10^{-6}$					AT LOAD MAX: (N)	30	4.5																																		
WEIGHT (Kg)	0.85																																									
OVERTEMPERATURE PROTECTION (ELECTRONICS): 75°C																																										
AMBIENT TEMPERATURE -10~50°C [14°F ~ 122°F]																																										
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)																																										
INSULATION CLASS B 130° [266°F]																																										
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)																																										
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)																																										
						APVD	<i>X.W.</i>	01.07.15	<b>PLUG&amp;DRIVE MOTOR</b>																																	
B	-	14.01.16	A.S.			CHKD																																				
A	-	18.11.15	A.S.	Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- cH	Work piece edge DIN ISO 13715	DRN	<i>A.S.</i>	01.07.15	DWG.NO PD2-CB42C048040-E-01																																
REV	DESCRIPTION	DATE	DRN				SIGNATURE	DATE																																		