



| Thread code TSCA    |                |
|---------------------|----------------|
| Thread type         | Trapezoid      |
| Major diameter [mm] | 9.820...10.000 |
| Minor diameter [mm] | 7.191...7.500  |
| Lead                | 2              |
| Pitch               | 2              |
| Starts              | 1              |
| Thread per inch     | 12.7           |

|     |             |      |     |   |                                       |  |                                  |   |            |
|-----|-------------|------|-----|---|---------------------------------------|--|----------------------------------|---|------------|
|     |             |      |     |    | Surface specification<br>DIN ISO 1302 | General tolerances<br>DIN ISO 2768- mK | Work piece edge<br>DIN ISO 13715 | Scale:<br>Material: 1.4305              |            |
|     |             |      |     | <br><b>Nanotec</b> <sup>®</sup><br>PLUG & DRIVE |                                       |  | Name                             | Date                                    |            |
|     |             |      |     |   | DRN                                   | X T                                    | 29.04.2020                       | THREADED SPINDLE<br>SCREW-AAA-TSCA-1000 |            |
|     |             |      |     |   | CHKD                                  | GYQ                                    | 29.04.2020                       |   |            |
| REV | DESCRIPTION | DATE | DRN |   |                                       |  | APVD                             | P.R.                                    | 29.04.2020 |