




Front view and mounting



Side view



Rear view



CONNECTION		BIPOLAR PARALLEL																															
SPECIFICATION																																	
VOLTAGE (VDC)	2.47		⚠																														
AMPS/PHASE	9.5																																
RESISTANCE/PHASE (Ohms)@25°C	0.35±15%	⚠	⚠																														
INDUCTANCE/PHASE (mH) @1KHz	2.7±20%																																
HOLDING TORQUE (Nm) [lb-in]	9.33 [82.57]																																
DETENT TORQUE (Nm) [lb-in]	0.2 [1.7]																																
STEP ANGLE (°)	1.8																																
STEP ACCURACY (NON-ACCUM)	±5%	⚠	⚠																														
ROTOR INERTIA (Kg-m ²) [lb-in ²]	3.0x10 ⁻⁴ [1.025]																																
WEIGHT (Kg) [lb]	4.6 [10.14]		⚠																														
TEMPERATURE RISE: MAX.80°C (MOTOR STANDSTILL; FOR 2 PHASE ENERGIZED)																																	
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]																																	
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)																																	
INSULATION CLASS B 130° [266°F]																																	
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)																																	
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)																																	
		PERMISSIBLE RADIAL+AXIAL FORCE																															
		ROTOR SPRING-MOUNTED IN AXIAL DIRECTION																															
		M16 MOTOR																															
		<table border="1"> <thead> <tr> <th>CABLE NO.</th> <th>ASSIGNMENT</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>A</td> </tr> <tr> <td>2</td> <td>A\</td> </tr> <tr> <td>3</td> <td>B</td> </tr> <tr> <td>4</td> <td>B\</td> </tr> <tr> <td>5</td> <td>HOUSING</td> </tr> </tbody> </table>		CABLE NO.	ASSIGNMENT	1	A	2	A\	3	B	4	B\	5	HOUSING																		
CABLE NO.	ASSIGNMENT																																
1	A																																
2	A\																																
3	B																																
4	B\																																
5	HOUSING																																
		<table border="1"> <thead> <tr> <th>AXIAL-FORCE Fa (N)</th> <th colspan="4">Fa=65</th> </tr> <tr> <th>DISTANCE a (mm)</th> <th>5</th> <th>10</th> <th>15</th> <th>20</th> </tr> <tr> <th>RADIAL-FORCE Fr (N)</th> <th>535</th> <th>355</th> <th>256</th> <th>200</th> </tr> <tr> <th></th> <th>AXIAL</th> <th colspan="3">RADIAL</th> </tr> <tr> <th>SHAFT PLAY (mm)</th> <td>0.075</td> <td colspan="3">0.025</td> </tr> <tr> <th>AT LOAD MAX: (N)</th> <td>10</td> <td colspan="3">5.0</td> </tr> </thead> </table>		AXIAL-FORCE Fa (N)	Fa=65				DISTANCE a (mm)	5	10	15	20	RADIAL-FORCE Fr (N)	535	355	256	200		AXIAL	RADIAL			SHAFT PLAY (mm)	0.075	0.025			AT LOAD MAX: (N)	10	5.0		
AXIAL-FORCE Fa (N)	Fa=65																																
DISTANCE a (mm)	5	10	15	20																													
RADIAL-FORCE Fr (N)	535	355	256	200																													
	AXIAL	RADIAL																															
SHAFT PLAY (mm)	0.075	0.025																															
AT LOAD MAX: (N)	10	5.0																															
3	revise drawing	30.08.16	A.S.		APVD	S.H.	22.07.08	STEPPER MOTOR IN PROTECTION																									
2	NEW VALUE OF RESISTANCE	31.03.10	J.W.		CHKD																												
1	RESTRICTION SUP.+EMF+WEIGHT	02.03.10	J.W.	Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- cH	Work piece edge DIN ISO 13715	DRN	J.W.	22.07.08	DWG.NO																							
REV	DESCRIPTION	DATE	DRN				SIGNATURE	DATE		AP8918L9504																							