



10 CONNECTOR A	
TWINTUS / 18-Pole / female / angled	
Crimp Contact:	7.010.980.802 (18x)
M16 Inserts, 18-Pole:	7.003.988.102
M16 Connector:	7.831.400.000
Contact Resistance	mΩ <3
Contact Material	Nickel- and Gold-Plated
Contact Carrier Material	PA 6, PBT
Connector Body Material	Copper-Zinc Alloy, Nickel-Plated
Coupling (Nut / Screw)	Copper-Zinc Alloy, Nickel-Plated
O-Ring Material	NBR
Protection Class	IP67 (locked Condition)

Function	Pin No.	Color
Output 1	1	WH/YE
Output 2	2	YE/BN
Output 3	3	WH/GY
Analog Input	4	WH/BU
+UB extern	5	WH/PK
GND (W001)	6	RD
RS485 Tx+	7	GY
RS485 Tx-	8	PK
RS485 Rx-	9	YE
RS485 Rx+	10	GN
Input 1	11	BK
Input 2	12	VT
Input 3	13	GY/PK
Input 4	14	RD/BU
Input 5	15	WH/GN
Input 6	16	BN/GN
CAN -	17	WH
CAN +	18	BN

20 CABLE SPECIFICATION		
LAPP UNITRONIC LiYCY (TP)		
Cable Length	mm	4960
Cable Diameter	mm	8.9
Cable Material		PVC
Cable Color		Grey
Conductor Insulation		PVC
Conductor / Cross - Section	mm ²	12x2x0.14
UL Type		No
Shielded		Yes
Bending Radius (flexible)		Min. 15 x Ø
Bending Radius (stationary)		Min. 6 x Ø

30 Cable End Sleeve		
Cable End Sleeve	(18x)	8 mm, Grey

GENERAL SPECIFICATION		
Rated Current	A	3
Rated Voltage	VAC/DC	24
Insulation resistance	MΩ	>10 ³
Ambient temperature		-5°C...+70°C

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715
05	revise drawing	Schneid_A	30.01.2019
REV	Rev. Text	Name	Rel. Date

Date		Name		Weight: 0.6 kg
Drawn	24.04.2018	Schneid_A		
Checked	30.01.2019	Reith_S		
Approved	30.01.2019	Schneid_A		ZK-TW-18-5M-2
14200103				
State: Released		Rev: 05		P

